



HigherDOSE
GET HIGH NATURALLY

INFRARED MAT PEMF THERAPY

BENEFICIAL LAYERS

AMETHYST LAYER

Provides a deeper penetration of therapeutic infrared. A natural tranquilizer known to relieve stress/anxiety and balance mood swings.

TOURMALINE LAYER

Provides a deeper penetration of therapeutic infrared. Known to increase mental alertness, improves circulation and strengthens the immune system.

CHARCOAL LAYER

Amplifies detoxification process.

CLAY LAYER

Emits negative ions and is balancing to the heat.

PEMF LEVELS

LEVEL 1 - 3Hz

Delta brain wave for sleep

LEVEL 2 - 7.8Hz

Theta brain wave when dreaming

LEVEL 3 - 10Hz

Alpha brain wave deep relaxation and meditation

LEVEL 4 - 23Hz

Beta brain for focus and alertness



FAR INFRARED

LOW EMF HEATING

MEDICAL GRADE MAGNETIC THERAPY

Magnetic therapy improves blood circulation.

PREMIUM MATERIALS

High-grade, non-toxic materials.

CRYSTAL THERAPY

The mats are built with a thick layer of 100% natural purple amethyst crystals in mesh fabric tubes across the entire mat. The amethyst and tourmaline layers provide an even deeper therapeutic DOSE of infrared.

PEMF TECHNOLOGY

The PEMF (Pulsed Electromagnetic Field) technology used in the Mat is based on optimized frequency, intensity and wave type of the pulsed electromagnetic field and to work in synergy with the other therapies which are part of the mat design; Far Infrared Therapy, Negative Ion Therapy, and Crystal Therapy

HAND HELD CONTROLLER



Seven temperature settings ranging from 30°-70° C / 86°-158° F

PEMF has 4 levels of Hz frequency (3Hz-23Hz)
Plus auto variation setting

TRAVEL FRIENDLY



Easily folds into travel-friendly size for compact storage and transportation

DOSE SAFELY



Features a thermal cutoff to prevent overheating as well as an automatic shutoff after a 20 min cycle

PLUG IN ANYWHERE



Uses standard residential power outlet

SPECIFICATIONS

Size

73.5 x 185 cm
(29" x 73")

Weight

19.5kg / 43lb

Power

Voltage
USA: 110V
UK: 230V
EU-non UK: 220-240V
Wattage
USA: 180W EU: 250W

PEMF info

4pcs PEMF cores implanted

Four (4) levels of Hz frequency 3Hz-23Hz

Heaters

Mats run in a very safe zone of 0.2-0.8 milligauss.
(Global TOC criteria is 2 milligauss.)
Electrical field: Low EMF

Limited 1-Year Warranty

Materials
Workmanship